

CONFIDENTIAL & PROPRIETARY

All data contained in this document is sole property of DRY SYSTEMS TECHNOLOGIES and is considered confidential and proprietary. This document may not be reproduced, released to third parties, or used for purposes other than for which it was furnished, without express written consent of DRY SYSTEMS TECHNOLOGIES. This document remains property of DRY SYSTEMS TECHNOLOGIES and must be returned upon request.







| BILL of MATERIAL | | | | | | | |
|------------------|-----|--------------|---------------------------------|----------|--|--|--|
| ITEM | QTY | PART NUMBER | DESCRIPTION | | | | |
| 1 | 1 | M500-521-01 | ALTERNATOR, 12 VOLT | REF 7-07 | | | |
| 2 | 1 | M500-530-01 | PULLEY - CUMMINS (INCL IN ALT.) | | | | |
| 2 ALT | 1 | M500-527-01 | PULLEY - ISUZU | | | | |
| 2 ALT | 1 | M500-521-106 | PULLEY - CATERPILLAR | | | | |
| 3* | 2 | M500-521-200 | FUSE, 20A | | | | |
| 4* | FT | M261-514-01 | CONDUIT HOSE, 3/4 ID | | | | |
| 5* | FT | M261-517-01 | CABLE, MULTICONDUCTOR, 12/3 | | | | |
| 6* | 1 | M261-512-01 | LIGHT SWITCH BOX, DUAL SWITCH | REF 7-12 | | | |
| 6 ALT | 1 | M261-522-01 | LIGHT SWITCH BOX, DUAL SWITCH | | | | |
| 7* | 6 | M261-502-01 | HEADLIGHT ASS'Y 12 VOLT, 50W | REF 7-09 | | | |
| | | M261-511-01 | LAMP, 12 VOLT, 50W | | | | |
| 8* | 7 | M261-505-01 | PACKING GLAND, 3/4 STRAIGHT | | | | |
| 9* | 7 | M261-506-01 | PACKING GLAND, 3/4 ELBOW | | | | |
| 10* | 7 | M261-507-01 | PLUG | | | | |
| 11* | 1 | M261-520-01 | EVALUATION TAG | | | | |
| | | M261-515-01 | KIT (includes *) | | | | |
| 12 OPT | 1 | M261-513-01 | CONNECTION BOX | | | | |
| ALT | | M261-523-01 | LAMP, 12 VOLT, 35W | | | | |

- 1. The Electrical System Schematic Diagram is drawing M261-012-01
- 2. The Electrical Permissibility Checklist is M261-008-01
- 3. A Diesel Electric Evaluation plate shall be located in the operator's compartment and shall be attached with adhesive or mechanical fasteners.

| TOLERANCES | | | | ΠΟΥ ΟΥΟΤΕΜΟ | DESCRIPTION | | | NO REOD | |
|---|-----------|--|---|--|-------------|-----------------------|---------------------|----------|----------------|
| Linear unless noted Machined: ±0.005 | | | | TECHNOLOGIES | | DATE JUNE 18, 2010 | DRAWN BY R GIBBS | <u> </u> | |
| Fabricated: ±0.01 | | | | 8102 LEMONT ROAD, SUITE 700 | MATERIAL | | APPROVED BY | | and the second |
| Angular: ±1/2° Surface finish 125 | 01 REV | | M500-521-200 was M500-521-20 DESCRIPTION | WOODRIDGE, IL 60517 Phone: 630-427-2051 Fax: 630-427-1036 E-Mail: eng@drysystemstech.com | DRAWING NO | M261-017 | 7-01 | | |

SECTION 7-03